



XX	Crimpeinsatz <i>crimp insert</i>	6kt.1 x Länge <i>hex1 x length</i>	6kt.2 x Länge <i>hex2 x length</i>	Abisoliermaße <i>stripping instruction</i>	
28	N01001A0028	1.69x2.5	3.45/4.52x15	③ Doppelcrimpung <i>double crimp</i>	
05	N01001A0005	1.69x2.5	5.41x8	① Stecker <i>plug</i> ④ Buchse <i>jack</i>	
24	N01001A0023	1.25x2.5	3.25x8	②	

i	12656	06.07.01	MA
h	12401	14.03.01	BJ
g	10729	13.08.99	BJ
f	10443	27.05.99	BJ
Index <i>index</i>	Änderung <i>modification</i>	Datum <i>date</i>	Name <i>name</i>

	Datum <i>date</i>	Name <i>name</i>
Gez. <i>drawn</i>	20.10.92	JB
Gepr. <i>app'd</i>	25.11.91	MaH

**Serie Mini UHF crimp  
Series Mini UHF crimp**

Unterr. <i>Art</i>	TG-Nr. <i></i>
R	T00100B1300



Original <i>original</i>	A4	Blatt <i>sheet</i>	1/1
-----------------------------	----	-----------------------	-----

Maßstab <i>scale</i>	2:1
-------------------------	-----

Ersatz für/  
replacement for  
Zeichnung vom 25.11.91