

PRODUCT-DETAILS

TY29M

CABLE TIE 120LB 30IN NATURAL NYLON



General Information

Extended Product Type	TY29M
Product ID	7TAG009330R0012
EAN	5414363063698
Catalog Description	CABLE TIE 120LB 30IN NATURAL NYLON
Long Description	High Performance Cable Tie, Natural Color Nylon 6.6, Length of 770mm (30.3 Inches) for Bundle Diameter up to 229mm (9.02 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F)

Ordering

EAN	5414363063698
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.024 lb 10.884 g
--------------------	---------------------

Container Information

Package Level 2 Units	500 piece
Package Level 2 Width	7.3 in 185 mm

Package Level 2 Height	6 in 152 mm
Package Level 2 Depth / Length	32.1 in 815 mm

Additional Information

Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES
UPC	786210830674

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY29M
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY29M

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

