

## Datasheet

# RS Pro 2 Way G DIN Rail Earth Block, Screw Down 22 to 11 AWG, 56mm length, Green/Yellow

RS Stock No: **815-767**



## Product Details

RS Pro 2-way G DIN rail earth block has a nylon housing construction in green and yellow colour. This earth block has screw down terminal and is suitable for grounding and earthing of 11 to 22 AWG wires. It measures 56 x 8 x 51.5 mm.

## Features and Benefits

- 2-Way G DIN rail earth block
- Nylon housing construction
- Green and yellow colour
- Suitable for grounding and earthing of 11 to 22 AWG wires
- Measures 56 x 8 x 51.5 mm

**Specifications:**

Cable CSA	4 mm <sup>2</sup>
Colour	Green/Yellow
Earth Block Type	G DIN Rail
Height	51.5 mm
Housing Material	Nylon
Length	56 mm
Maximum Operating Temperature	+105°C
Minimum Operating Temperature	-40°C
Number of Ways	2
Termination Method	Screw Down
Width	8 mm
Wire Size	22 to 11 AWG
Standards Met	IEC; UL Listed; CSA Certified