



TABLE 1

SHRINK BOOT CUT CONNECTOR	SHRINK BOOT CUT LENGTHS (IN) ± .125				LENGTH FROM END TO BOOT E ± .125
	A	B	C	D	
-----	3.13	2.00	1.38	1.00	.40

ALL DIMENSIONS ARE NOMINAL. SHRINK BOOTS IN ORDER OF ASSEMBLY AS SHOWN.

TABLE 2

DASH NO.	LENGTH	MAX LOSS
-1	19.69 ± 1.00	1.10 DB
-2	39.37 ± 1.00	1.80 DB
-3	78.74 ± 1.00	3.25 DB
-4	118.11 ± 1.00	4.70 DB

OBsolete

NOTES:

- ELECTRICAL SPECIFICATIONS:  
FREQUENCY: .05 TO 18.0 GHz  
MAX VSWR: 1.35:1  
MAX LOSS: SEE TABLE 2

2. DUST CAP FOR SMA PLUG TO BE FITTED  
DUST CAPS NOT SHOWN FOR CLARITY.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.

LOC  
E  
DIST  
B

P	LTR	REVISION RECORD	DATE	DWN	APVD
A	EBD0-0398-04		04OCT04	RS	NC
B	EBD0-0113-05		10MAR05	RS	NC
C	ECR-05-006209		11JUL05	RS	NC

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± -
ANGLES ±	-
SURFACE TEXTURE	

DWN R.SMITH	04OCT04	MATERIAL -	HEAT TREAT -
CHK S.SHACKSON	04OCT04	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
APVD N.CANN	04OCT04		
NAME COAXIAL CABLE ASSEMBLY, TEST			
SCALE NTS	SIZE A2	DRAWING NO 1814403	SHEET 1 OF 1
		REV C	