

Nitrile disposable gloves that provide confident grip and durable protection

- **Enhanced grip:** Featuring our Mega Texture surface for consistent grip in wet and dry conditions
- **Tear resistance:** Robust 0.13mm/5.1mil palm thickness to resist tearing in use
- **High visibility:** Orange color to increase visibility while working
- **Durable:** Strong formulation providing durable yet comfortable hand protection
- **Food approved:** Ideal for a wide range of food handling applications



Industries

- Automotive
- Automotive Aftermarket
- Food Processing
- Machinery and Equipment
- Maintenance
- Manufacturing
- Recycling and Waste Disposal
- Transportation

Recommended For

- General Purpose Auto Aftermarket
- Food processing and handling
- Oil, fluids and filter change
- Engine transmission and repair
- Mechanical jobs
- Maintenance
- Tire rotation & changes
- Vehicle maintenance
- Assembly of parts

TECHNICAL DATA SHEET

	Product Information
External Glove Surface	Fully Textured
Audit Standards	ISO 13485, ISO 9001
Product Certification	Arrette du 05/08/2020, EU Food Contact Approved, EC 2023/2006, ASTM D6319, CE 0493, EN ISO 21420:2020, EN ISO 374-1:2016+A1:2018 Type B JKPT, EN ISO 374-5:2016, FDA21 CFR 177-2600-US Food Contact Approved, ISO 13485, ISO 9001, ISO 18889:2019 G1, UKCA
Packaging Overview	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Thailand
Product Segmentation	Robust
Antistatic	Yes
Silicone Free	No

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240/9.45		ASTM D6319,ASTM D3767
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1,EN 374-2
Palm Thickness (mm/mils)	0.13/5.1		ASTM D6319,ASTM D3767
Finger Thickness (mm/mils)	0.16/6.3		ASTM D6319,ASTM D3767
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥500	≥400	ASTM D412 & D573
Force at break (N)	≥6	≥6	EN 455-2

ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	93256070	93256080	93256090	93256100	93256110

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region
MY: +603 8310 6688
apac.medical@ansell.com
CN: +86 21 38275000
infochina@ansell.com
JP: +813 5549 8151
info.medical.jp@ansell.com

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region
BR: +55 (11) 3356-3100
latam.medical@ansell.com
MX: +52 442 296 2050
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

Australia
Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia
Ansell PYC
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

