

General Information

Extended Product Type:	CR515
Product ID:	7TCA083220R0010
EAN:	5414363080282
Catalog Description:	5/8 IN TYPE G CONNECTOR CLAMP
Long Description:	Rod to Cable Clamp - Nominal Rod Diameter 5/8 Inch 16mm, Maximum Conductor 16-70 millimeters squared

Categories

Products » Low Voltage Products and Systems » Protection, Connection & Wire Management » Wire Management and Connectivity » Grounding, E&LP

Ordering

EAN:	5414363080282
Minimum Order Quantity:	10 piece
Customs Tariff Number:	7419910050

Dimensions

Product Net Width:	304.8 mm
Product Net Height:	127 mm
Product Net Depth:	215.9 mm
Product Net Weight:	0.55 kg

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	304.8 mm
Package Level 1 Height:	127 mm
Package Level 1 Length:	215.9 mm
Package Level 2 Units:	200 piece
Package Level 2 Width:	1371.6 mm
Package Level 2 Height:	279.4 mm
Package Level 2 Length:	685.8 mm
Package Level 3 Units:	9600 piece

Additional Information

Product Main Type:	LIGHTNING PROTECTION
Product Name:	CAST, MOULDED, STAMPED OR FORGED,
UPC:	786210342160

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	CR515
------------------------------------	-------

Classifications

UNSPSC:	39121613
---------	----------

