



Product data sheet

Power tools for trade & industry

Random Orbit Sander

PRO GEX 12V-77



Efficient spot sanding for excellent surface finishings

The most important data

Sanding pad diameter	77 mm
Orbit diameter	2.5 mm
No-load speed	3,000 – 8,000 rpm

Part Number 0 601 9L2 100

Technical data

Technical data

Sanding pad diameter	77 mm
No-load speed	3,000 – 8,000 rpm
Orbital stroke rate	6,000 – 16,000 opm
Eccentricity	1.25 mm
Weight excl. battery	0.52 kg
Orbit diameter	2.5 mm
Packaging dimensions (width x length x height)	123 x 197 x 72 mm
Battery voltage	12.0 V
BITURBO	No

Noise/vibration information

Sanding solid wood

Vibration emission value ah	1.6 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Strong performance with powerful Bosch Professional 12V system and brushless motor
- Excellent ergonomics thanks to small, compact shape and comfortable grip
- Convenient tool operation with HMI for easy speed setting and battery status indication

**HEAVY
DUTY****3000-
8000**
min⁻¹/rpm**L-BOXX
READY****PROFESSIONAL
12V
SYSTEM**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

