




Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Grommet**

Primary Product Material: **Flexible PVC**

Primary Product Color: **Black**

Packaging Method: **Bag**

Packaging Quantity: **500**

Features

Product Type Features

Strain Relief Accessory Type	Grommet
------------------------------	---------

Body Features

Primary Product Material	Flexible PVC
Primary Product Color	Black

Dimensions

Product Length	10.67 mm[.42 in]
Product Height	9.53 mm[.375 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Packaging Features

Packaging Method	Bag
Packaging Quantity	500

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 350522-1
09P STR/REL HSG HNGD V0

TE Part # 350523-1
15P STR/REL HSG HNGD V0

TE Part # 350374-1
12P STR/REL HSG HNGD V0

Also in the Series | AMP Miniature Rectangular MR

Connector Caps & Covers(15)

Connector Contacts(20)

Connector Hardware(2)

Connector Strain Relief(9)




PCB Headers & Receptacles(57)



Power Contacts(20)




Rectangular Power Connectors(77)




Wire-to-Board Headers & Receptacles (57)

Customers Also Bought




TE Part #1-2273127-3
M12 angld sckt to M12 strght plg 3 LED



TE Part #350374-1
12P STR/REL HSG HNGD V0



TE Part #53242-6
PG SPR SPD 22-16COM22-18MIL 10



TE Part #G-NICO-023
0.1 DEG C ACCURACY QFN TEMP SENSOR




TE Part #MS580330BA01-00
MS5803-30BA01 DIGIT PRESSURE SENSOR



TE Part #0413-003-1605
SEALING PLUG, SIZE 16, BLU



TE Part #2232227-1
DUST COVER FOR PV4 SOCKET



TE Part #2-380935-0
MR SPLT GROMMET .437 DIA BLK LF



TE Part #1011-243-0805
BKSHL, 8P, BLK, PLG, ST, NW8.5/10/13



TE Part #DT06-08SB-C015
PLG, 8P, BLK, E, B

Documents

Product Drawings

MR SPLIT GROMMET .281 DIA BLK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-350380-1_V.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2-350380-1_V.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-350380-1_V.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG](#)

English

Product Specifications

[Application Specification](#)

English