

8096SL
Lifting chain slings, 1 leg, with self-locking and clevis grab hooks, grade 8

CE

EN 818-4

TECHNICAL DATA

- safety factor: 4
- chain-sling identification tag

ATTACHED CERTIFICATES

- Manufacturer's Certificate UNI EN818-4
- CE Declaration of Conformity

AVAILABLE CERTIFICATES

- Technical product specifications



	art.	 D mm	L m	WLL ton
080960201	8096SL D6-1	6*	1	1,12
080960202	8096SL D6-2	6*	2	1,12
080960203	8096SL D6-3	6*	3	1,12
080960204	8096SL D6-4	6*	4	1,12
080960221	8096SL D7-1	7*	1	1,5
080960222	8096SL D7-2	7*	2	1,5
080960223	8096SL D7-3	7*	3	1,5
080960224	8096SL D7-4	7*	4	1,5
080960241	8096SL D8-1	8*	1	2
080960242	8096SL D8-2	8*	2	2
080960243	8096SL D8-3	8*	3	2
080960244	8096SL D8-4	8*	4	2
080960251	8096SL D10-1	10*	1	3,15
080960252	8096SL D10-2	10*	2	3,15
080960253	8096SL D10-3	10*	3	3,15
080960254	8096SL D10-4	10*	4	3,15
080960331	8096SL D13-1	13*	1	5,3
080960332	8096SL D13-2	13*	2	5,3
080960333	8096SL D13-3	13*	3	5,3
080960334	8096SL D13-4	13*	4	5,3
080960361	8096SL D16-1	16*	1	8
080960362	8096SL D16-2	16*	2	8
080960363	8096SL D16-3	16*	3	8
080960364	8096SL D16-4	16	4	8
080960401	8096SL D20-1	20	1	12,5
080960402	8096SL D20-2	20	2	12,5
080960403	8096SL D20-3	20	3	12,5
080960404	8096SL D20-4	20	4	12,5