

## FEATURES

- **±2.5 % Accuracy:** Ensures reliable and precise pressure readings
- **Calibrated:** Ready for immediate use with accurate measurements
- **Stainless Steel Case Material:** Offers durability and corrosion resistance
- **Right Connection Location:** Facilitates convenient installation in various setups
- **1/4 in NPT Male & 3/8 in NPT Female Pressure Connection:** Provides versatility in connection options
- **White Dial Colour:** Enhances visibility and readability of measurements

## RS PRO Pressure Gauge & Mounting Block, 63 mm Dial

RS Stock No: 291-728



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

## Product Description

This RS PRO pressure gauge and mounting block is designed for precise pressure measurement in industrial applications. With a dial size of 63 mm, it provides clear and accurate readings from 0 to 1000 bar, making it ideal for high-pressure environments. The stainless steel construction ensures durability and resistance to corrosion, while the threaded connection allows for easy installation.

## General Specifications

Calibrated	Yes
Connection Location	Right
Connection Size	1/4 in, 3/8 in
Connection Type	Threaded
Pressure Connection	1/4 in NPT Male & 3/8 in NPT Female
Product Type	Pressure Gauge & Mounting Block

## Measurement Specifications

Accuracy	±2.5 %
Maximum Pressure Measurement	1000 bar
Minimum Pressure Measurement	0 bar

## Mechanical Specifications

Case Material	Stainless Steel
Dial Colour	White
Dial Size	63 mm

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, CE, EN ISO 12100:2010, EN 809:1998+A1:2009, RoHS, UKCA
---------------------	--

