

PRODUCT DATASHEET P CLAS P 60 7 W/4000K E27

PARATHOM Retrofit CLASSIC P DIM | Dimmable LED lamps, classic bulb shape



AREAS OF APPLICATION

- Domestic applications
- General illumination
- Outdoor use in outdoor luminaires only (minimum IP65)
- Perfect for decorative installations

PRODUCT BENEFITS

- Design, dimensions, luminous flux comparable to an incandescent lamp
- Very low energy consumption
- Robust against vibrations
- Lamps with innovative LED "filament" technology
- Instant 100 % light, no warm-up time
- Can be easily fitted instead of ordinary light bulbs

PRODUCT FEATURES

- Professional LED lamps for line voltage
- Dimmable (with many common dimmers, see also www.ledvance.com/dim)
- Mercury-free lamps
- Lifetime: up to 15,000 h
- Beam angle: up to 300°



TECHNICAL DATA

Electrical data

Rated wattage	7.00 W
Nominal wattage	7.00 W
Nominal voltage	220240 V
Max. lamp no. on circuit break. 10 A (B)	306
Max. lamp no. on circuit break. 16 A (B)	490
Operating frequency	5060 Hz
Power factor λ	> 0.70
Claimed equiv. conventional lamp power	60 W


Photometrical data

Nominal luminous flux	806 lm
Rated luminous flux	806 lm
Rated color temperature	4000 К
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Cool White
Color temperature	4000 К
Luminous flux	806 lm
Color rendering index Ra	≥80
Standard deviation of color matching	≤6 sdcm

Light technical data

Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

Dimensions & weight



Overall length	105.0 mm
Diameter	60.0 mm

PRODUCT DATASHEET

Outer bulb	A60
Length	105.0 mm

Temperatures & operating conditions

Maximum temperature at tc test point	50 °C

Lifespan

Nominal lamp life time	15000 h
Rated lamp life time	15000 h
Number of switching cycles	100000

Additional product data

Base (standard designation)	E27	
Mercury content	0.0 mg	
Mercury-free	Yes	
Show WEEE picto	Yes	
Product remark	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value	

Capabilities

Dimmable	Yes
----------	-----

Certificates & standards

Energy efficiency class	A++
Energy consumption	7 kWh/1000h

Country-specific categorizations

Order reference	LEDPCLA60D 7W/8
-----------------	-----------------

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075287426	Folding carton box 1	60 mm x 60 mm x 111 mm	45.00 g	0.40 dm ³
4058075287433	Shipping carton box 10	325 mm x 136 mm x 126 mm	543.00 g	5.57 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.