



Product data sheet

Power tools for trade & industry

Cordless Press Tool

PRO GPT 18V-19



Compact and fast, the 18 V press tool with the power of 19 kN

The most important data

Pressing force max	21 kN
Comp range dia max plastic	40 mm
Comp range dia max metall	35 mm

Part Number 0 601 9M2 000

Technical data

Description

Product category subdivision	Cordless Press Tool
Head rotation	360 °
Pressing force max	21 kN
Time pressing cycle	3 s
Comp range dia max metall	35 mm
Comp range dia max plastic	40 mm
Calibration Interval	40.000 cycles
BITURBO	No
Weight	2.5 kg
Weight excl. battery	2.5 kg

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Makes working in tight spaces easy with compact design and 360° rotatable head
- Fast, comfortable working – pressing cycles take less than 3 seconds
- Convenient and robust thanks to the battery protection cover

