



ENGLISH

Datasheet

RS Pro Bright Zinc Plated Steel Nylon Insert Locking Nut, M4

RS Stock No: **524-304**



Product Details

RS Pro nylon insert locking nut made of bright zinc plated steel offers corrosion resistance. This nut is self locking due to glass filled nylon insert and features M4 metric internal threading to couple with threaded rod. The nut is designed to remain secure despite conditions of severe vibration.

Features and Benefits

- Grade 8 steel, bright zinc plated
- M4 metric threading
- Self-locking due to glass filled nylon insert
- Remain secure despite conditions of severe vibration

**Specifications:**

Finish	Bright Zinc Plated
Material	Steel
Thread Size	M4
Type	Nylon Insert
Grade	8
Specification	DIN 982
Thickness	5.52 to 6 mm
Thread Pitch	0.7
Width Across Corners	7.66 mm
Width Across Flats	6.78 to 7 mm
Wrenching Height	2.32 mm

M4 x 10 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9636	M4 x 16 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9642	M4 x 20 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9658	M4 x 30 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9664
M6 x 12 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9759	M6 x 16 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9771	M6 x 20 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9787	M6 x 25 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9793
M8 x 16 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9850	M8 x 20 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9866	M8 x 30 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9872	M8 x 40 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9888
M8 x 40 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9888	M4 Nylon insert nuts/Muttern nyloneinsatz/Tuercas con inserto de nailon/Ecrous à filets rapportés en nylon/Dadi di nylon a intagli  524-304	M6 Nylon inserts nuts/Muttern Nyloneinsatz/Tuercas con inserto de nailon/Ecrous à filets rapportés en nylon/Dadi di nylon a intagli  524-326	M8 Nylon insert nuts/Muttern Nyloneinsatz/Tuercas con inserto de nailon/Ecrous à filets rapportés en nylon/Dadi di nylon a intagli  530-393
M4 Nuts/Muttern/Tuercas/Ecrous/Dadi  525-896 M4 Washers/Unterlegscheibe/Arandela/Rondelles/Rondella  525-925	M6 Nuts/Muttern/Tuercas/Ecrous/Dadi  525-919	M8 Nuts/Muttern/Tuercas/Ecrous/Dadi  527-612	M6 Plain washers/Unterlegscheibe/Arandela plana/Rondelles plates/Rondella piana  525-947
M8 Plain washers/Unterlegscheibe/Arandela plana/Rondelles plates/Rondella piana  527-634	M10 Plain washers/Unterlegscheibe/Arandela plana/Rondelles plates/Rondella piana  527-640	M10 x 20 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  232-8518	M10 x 20 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  232-8518

M10 x 30 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  232-8546	M10 Nylon inserts nuts/Muttern Nyloneinsatz/Tuercas con inserto de nailon/Ecrous à filets rapportés en nylon/Dadi di nylon a intagli  530-400	M10 Nuts/Muttern/Tuercas/Ecrous/Dadi  527-628
--	---	---

M10 x 50 Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  232-8568
--