

Specifications



Photo is representative



Eaton FAZ-C25/3-NA

Eaton FAZ branch protector,UL 489 Industrial miniature circuit breaker - supplementary protector,Medium levels of inrush current are expected,25 A,10 kAIC, 14 kAIC,Three-pole,277/480 V,5-10X /n,50-60 Hz,Screw terminals,C Curve

General specifications

PRODUCT NAME	Eaton FAZ branch protector
CATALOG NUMBER	FAZ-C25/3-NA
EAN	4015081021284
PRODUCT LENGTH/DEPTH	2.1 in
PRODUCT HEIGHT	4.13 in
PRODUCT WIDTH	2.97 in
PRODUCT WEIGHT	0.8 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Std. C22.2 No. 235 UL 489
CATALOG NOTES	Positioned for medium inrush startup currents to provide protection for small transformers and pilot devices.



Powering Business Worldwide

Physical Attributes

NUMBER OF POLES	Three-pole
TERMINALS	Screw
TYPE	UL 489 Industrial miniature circuit breaker - supplementary protector

Miscellaneous

APPLICATION	Suitable for applications where medium levels of inrush current are expected
--------------------	--

Performance Ratings

AMPERAGE RATING	25 A
CIRCUIT PROTECTION	C curve
FREQUENCY RATING	50-60 Hz
INTERRUPT RATING	10 kAIC 14 kAIC
TRIP TYPE	5-10X /n
VOLTAGE RATING	277/480V

Resources

CATALOGS	Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - FAZ-C25/3-NA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

