

## PSZFON-1030 - PSZFON

General Part Information	
Product Description	PSZFON-1030
Article Number	33234
POPNut Type	<a href="#">i</a> PSZFON
Standard Bulk Pack Quantity	1,500

Geometry / Dimensions	
Thread Size	M10
Body Type (open / closed)	<a href="#">i</a> Open
Body Features	<a href="#">i</a> Linear Knurls
Body Length (mm)	17.30
Min. Grip Thickness (mm)	0.50
Max. Grip Thickness (mm)	3.00
Head Style	<a href="#">i</a> Flat Head
Hole Diameter (mm)	12.00
Head Diameter (mm)	15.80
Head Thickness (mm)	2.00
Barrel Diameter (mm)	11.90

Material / Weight	
Material	<a href="#">i</a> Steel
Weight per thousand (kg)	7.0

