

2885 - Preston Trousers

Collection: General Workwear

Range: Workwear

Shell Fabric: Kingsmill Polycotton: 65% Polyester, 35% Cotton, 245g

Outer Carton: 36

Product information

This classic style is durable and comfortable with a sewn in front crease which adds to the professional look. Features include two side pockets and a back jetted pocket.

Workwear

Portwest workwear offers a range of designs and features suitable for many end uses. Quality fabrics and construction techniques are used guaranteeing comfort and safety. Tested to withstand the rigours of everyday wear each garment has been carefully designed and manufactured to ensure optimum quality at the best price.



Features

- Incredibly durable and hardwearing
- Sewn in front centre seam for a tailored look
- 3 pockets for ample storage
- 1 Back pocket with button closure
- Hook and bar closure
- 2 Side pockets
- 40+ UPF rated fabric to block 98% of UV rays
- An improvement has been made to the current fit of the product
- Machine washable at 60°C
- Anti-scratch design with no exposed metal parts



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

2885 - Preston Trousers

Commodity Code: 6203431100

Test House

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
2885NAR26	Navy	43.0	28.0	50.0	0.4100	0.0602	5036108143023	15036108731791
2885NAR28	Navy	43.0	28.0	50.0	0.4000	0.0602	5036108056651	15036108602626
2885NAR30	Navy	43.0	28.0	50.0	0.4200	0.0602	5036108056668	15036108602640
2885NAR32	Navy	43.0	28.0	50.0	0.4200	0.0602	5036108056675	15036108602657
2885NAR34	Navy	43.0	28.0	50.0	0.4280	0.0602	5036108056682	15036108602688
2885NAR36	Navy	43.0	28.0	50.0	0.4520	0.0602	5036108056699	15036108602695
2885NAR38	Navy	43.0	28.0	50.0	0.4600	0.0602	5036108056705	15036108602718
2885NAR40	Navy	43.0	28.0	50.0	0.4760	0.0602	5036108056712	15036108602732
2885NAR42	Navy	43.0	28.0	50.0	0.5000	0.0602	5036108056729	15036108602763
2885NAR44	Navy	43.0	28.0	50.0	0.4980	0.0602	5036108056736	15036108602787
2885NAR46	Navy	43.0	28.0	50.0	0.5020	0.0602	5036108124107	15036108602794
2885NAR48	Navy	43.0	28.0	50.0	0.5400	0.0602	5036108124114	15036108602800
2885NAR50	Navy	43.0	28.0	50.0	0.5280	0.0602	5036108124121	15036108602817
2885NAR52	Navy	43.0	28.0	50.0	0.5460	0.0602	5036108143030	15036108602824