



BS 80-PP10

Flat Type Fuse, 80A

Product Properties:

Explosion-proof	No
Release characteristic	Medium time-lag
Optical defect indication	Yes
Type of current	DC
Colour code	Other
Nominal voltage DC	32 V
Max. continuous voltage DC	32 V
Number of fuses	10 .
Model	Other
Nominal current	80 A

Dimensions:

Width	41 mm
MOQ	10 .
Unit	pck
Mounting holes	M5
Centre-to-centre distance of connections	30 mm
Length	11 mm

Approvals:

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
REACH	No SVHC (250 Subs. 25 June 2025)
RoHS	RoHS 3 (2015/863)

SCIP

Not Applicable

Other information:

ETIM-Class	EC004122 - Strip fuse
ETIM-Release	DYNAMIC
Trademark	NECORE
Product Group	Bolt-on / Strip fuses - Pin-pac
Search Description	BLADSÄKRING, 80A
Alternative SKU	BS80-PP10

Logistic information:

Barcode	733117610378
Country of origin	TR
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	10 .
Stock code	BS 80-PP10
Taric code	85361090
Unit	pck

*We reserve the right to make technical changes and disclaim any typographical errors.