

## ELENA JJD23

**S3 SRC**  
**EN ISO 20345:2011**  
**35 to 42**



- **Aseptane™ upper**
- **J-DREAM dual-density TPU sole**

- ❖ **Aseptane™ upper** : Microfibre resistant to fluid projection, it is ideal for wet working conditions. Water-repellent, breathable, washable at 30° C.
  - ❖ Anti-bacterial nylon lining.
  - ❖ Vamp lining in non-woven fabric. Resists scuffing and acid perspiration.
  - ❖ Padded collar for extra comfort and better ankle and Achilles tendon protection.
  - ❖ Closure by black laces (90 cm). Padded textile tongue for good instep protection, combined with two side bellows to prevent any dirt from getting into the boots.
  - ❖ Heel stiffener to reinforce the heel seat.
  - ❖ **J-Souplesse** footbed : full piece, antistatic and anatomic, in soft polyurethane covered with a special fiber; perforated in the front part for better foot venting, cushioning effect in the heel area.
  - ❖ Antiperforation insert : **FleXtane™** Zero millimeter, made of textile composite materials, it protects 100 % of the support surface of the foot and it can't be detected by metal detectors. EN ISO 12568:2010 approved.
  - ❖ 200 Joules steel toe cap with perforations.
- **J-Dream dual density TPU sole, sporty profile :**

### Slip resistance tests results

EN Standard : EN ISO 20345 : 2011

**Requirement SRC (SRA+SRB)**

**SRA** Test ground : ceramic / lubricant : water and detergent

On flat **0,40** (>0,32) – On the heel **0,39** (>0,28)

**SRB** Test ground steel / lubricant : glycerine

On flat **0,19** (>0,18) – On the heel: **0,16** (>0,13)

- ✓ Abrasion resistance.
- ✓ Highly resistant to oils and hydrocarbons.
- ✓ Heel shock absorption 20 Joules.
- ✓ Anti-static.



Weight	Gross weight (38) : 1000 g / Net Weight (38) : 782 g							
Size	35	36	37	38	39	40	41	42
Packaging	10 pairs							
Dimensions	600 x 405 x 320							