

Star delta starter, enclosed, 400 V/15 kW, steel

Part no. XSDP15/ST(400V50HZ,440V60HZ)
Catalog No. 118553
Alternate Catalog No. XSDP15-STI3

Delivery program

| | | | |
|---|---|----|--|
| Product range | | | enclosed contactor combinations |
| Application | | | Star-delta motor starting for contactor combinations |
| Utilization category | | | NAC-3: Normal AC induction motors: starting, switch off during running |
| Max. rating for three-phase motors, 50 - 60 Hz | | | |
| AC-3 | | | |
| 380 V 400 V | P | kW | 15 |
| Actuating voltage | | | 400 V 50 Hz, 440 V 60 Hz |
| Voltage AC/DC | | | AC operation |

Technical data ETIM 7.0

| | | | |
|--|--|----|----------------------|
| Low-voltage industrial components (EG000017) / Combination of contactors (EC000010) | | | |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Contactor (LV) / Combination of contactor (ecl@ss10.0.1-27-37-10-09 [AGZ572014]) | | | |
| Function | | | Star-delta contactor |
| Rated control supply voltage Us at AC 50HZ | | V | 400 - 400 |
| Rated control supply voltage Us at AC 60HZ | | V | 440 - 440 |
| Rated control supply voltage Us at DC | | V | 0 - 0 |
| Voltage type for actuating | | | AC |
| Rated operation current Ie at AC-3, 400 V | | A | 29.3 |
| Rated operation power at AC-3, 400 V | | kW | 15 |
| Rated operation power NEMA | | kW | 0 |
| Type of electrical connection of main circuit | | | Screw connection |
| Degree of protection (IP) | | | IP55 |
| Degree of protection (NEMA) | | | Other |