



Cut



Medium Duty

Cut, oil and abrasion-resistant gloves, granting good grip in dry conditions

- **Optimized durability:** EDGE[®] 48-701 industrial gloves' palm PU coating provides a high level of abrasion protection (ANSI 6), moderate cut resistance (ANSI A2), a good grip in dry environments, and better protection against oil than knitted or cut and sewn safety work gloves
- **Increased protection:** EDGE 48-701 protective gloves provide two levels of cut performance, affording robust, all-round hand protection in mediumweight applications
- **Enhanced features:** A more affordable alternative to medium-duty leather, thick cotton or aramid gloves, EDGE[®] 48-701 high-quality work gloves offer a seamless liner and knitted wrist, which deliver form-fitting comfort, good dexterity and added wrist protection



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- Aeronautics
- Assembly line
- Assembling metal parts and components
- Handling sharp or irregular metal pieces
- Molding
- Plastic injections

Key Features

- **Palm PU coating:** High level of protection against abrasion and cuts
- **Two levels of cut performance:** For advanced hand protection gloves
- **Seamless liner and knitted wrist:** For flexible and secure work gloves

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4342B

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE [®] 48-701	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: HPPE, Spandex, Polyester Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	220-270 mm, 8.66-10.63 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699