

32 41

Socket 3/4"

hexagon UD profile

Code	ETIM
6271190	EC002203
EAN	UNSPSC
4010886627112	27-11-17-04
Country of origin	eCl@ss
Germany	21-04-02-18
Customs tariff number	
82042000	



Article description

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - D 20, ISO 1174, with locking pin
- Manually operated, with non-slip cross knurling
- Vanadium steel 31CrV3, matt chromium-plated

Article information

Contents (Qty of pieces)	1	Drive connector square female [inch]	3/4"
Net weight [kg]	0,593 kg	Standard	DIN 3124 ISO 2725-1 DIN 3120 - D 20 ISO 1174
Total length [mm]	63 mm	Width across flats 1 [mm]	41
Total width [mm]	57 mm	Backup	Locking pin
Total height [mm]	57 mm	Insert-Ø 1	57,1 mm
Surface	Matt chrome-plated	Working length	62,5 mm
Material	Chrome-vanadium steel 31CrV3	Insert-Ø 2	44,0 mm
Drive connector square female (metric)	20,0 mm	Operating depth	30,5 mm