

Datasheet

Switchgear Cable

8114551
5167928
8114542
5167906
8114554
5167956
8114558
5167934
8114567
5167940



Conductor: 84/0.30mm Plain Annealed Copper (Class 5 to IEC 60228)

Insulation: PVC (Type TI1 to BS EN 50363)

Insulation Radial Thickness: 0.80mm

Diameter Over Insulation: 5.30mm (Maximum)

Voltage Rating: 600/1000V

Conductor Resistance: 3.3 Ω /km @ 20°C (Nominal)

Cable Weight: 70.80 kg/km (Nominal)

Standard: BS 6231:2006