



PRODUCT DATASHEET

Datasheet creation date: 2025/07/09 7:47 (UTC)



6804DD

Single-Row Deep Groove Ball Bearings

Boundary Dimensions

d	20	mm	Bore diameter
D	32	mm	Outside diameter
B	7	mm	Width
r (min.)	0.3	mm	Chamfer dimension

Basic Load Ratings

Cr	4400	N	Basic dynamic load rating
C0r	2470	N	Basic static load rating

Speeds

Grease	13000	min-1	Grease lubrication
--------	-------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	22	mm	Diameter of shaft abutment
da (max.)	22	mm	Diameter of shaft abutment
Da (max.)	30	mm	Diameter of housing abutment
ra (max.)	0.3	mm	Radius of shaft or housing fillet

Calculation factors

fo	15.5		Factor
----	------	--	--------

Additional information

z	13		Number of Balls
Dw	3.5	mm	Ball Diameter

Mass

Mass approx.	0.017	kg	Mass approx.
--------------	-------	----	--------------

