

Datasheet

RS Pro 8 Port Sensor Box with 5 Way M12 Sockets

RS Stock No: 877-1224



Product Details

RS Pro sensor box has 8 ports and compatible 5-way M12 pin connector. It has selection of splitter boxes for M12 connecting leads, for use with sensor and automation equipment. With an excellent degree of environmental protection, this I/O junction box is suitable for harsh industrial conditions.

Features and Benefits

- Nickel plated brass contacts
- MODBUS and zigbee wireless models protected to IP55
- Wired and terminal block models protected to IP65/IP67
- PBT plastic housing
- Operating temperature range of 0 to +55°C
- Neoprene O-Ring

**Specifications:**

Cable Length	5 m
Compatible Connector	5-Pin M12
Connector Size	M12
Control Cable Connector	M12
Number of Ports	8
Number of Ways	5
Connection Type	Cable
Housing Material	PBT Plastic
IP Rating	IP65, IP67
Operating Temperature Range	0 to +55°C
Rated Current	2 A
Supply Voltage	24 V dc