



Main

Range	Exiway
Aesthetic name	Exiway Easyled
Product or component type	Emergency light fitting
Device application	Lighting
Function	Standard
Supply	Maintained Non-maintained
Number of batteries	1 x 3.6 V 1.6 Ah Ni-Cd (Nickel-Cadmium)
Colour	White
Light source	LED integral LED 4 x 1.5 W
Light source colour	White
Cover type	Transparent
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

[Ue] rated operational voltage	220...230 V AC 50 Hz
Power consumption in VA	3.8 VA non-maintained 5.9 VA maintained
Power consumption in W	0.8 W non-maintained 2.6 W maintained
Current consumption	15 mA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 H
Luminous flux	Maintained mode: 85 lm Emergency condition: 170 lm
Type of glass	Serigraphed transparent glass
Material	Plastic: housing Plastic: cover
Device mounting	Flush wall Surface wall Surface ceiling Flush false ceiling
Height	37 Mm
Width	292.5 Mm
Depth	116.5 Mm
Net weight	0.52 Kg

Environment

IP degree of protection	IP42
IK degree of protection	IK07
Ambient air temperature for operation	5...30 °C
Fire resistance	850 °C
Product certifications	AENOR ENEC
Standards	IEC 60695-2-10 EN/IEC 60598-2-22

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	589 G
Package 1 Height	4.5 Cm
Package 1 width	12.3 Cm
Package 1 Length	30 Cm
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Weight	7.555 Kg
Package 2 Height	30 Cm
Package 2 width	30 Cm
Package 2 Length	40 Cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**