

# Drummond Leads and Accessories

## Heavy Duty CAT IV Fused Leads



Drummond Heavy Duty CAT IV Fused Leads, 1.2m long and double insulated with a contrasting white inner core to identify damage. The unique 45° plug reduces cable stress, aids grip and improves connection.

- MP21-08 – 600V CAT IV fitted with 500mA 600V 50kA fuses
- MP30-08 – 1000V CAT IV fitted with 500mA 1000V 50kA fuses
- MP21-10BK – Heavy duty black crocodile clip
- MP21-10RD – Heavy duty red crocodile clip

## Test Lamp Probes



- MTL2106  
Straight Prod Long 130mm
- MTL2107  
Angled Prod Long 130mm
- MTL2108  
Straight Prod Australian 62mm
- MTL2104  
Straight Prod Standard 62mm
- MTL2105  
L Shaped Prod Standard 62mm
- MTL2103  
Straight Prod Short 30mm

**DRUMMOND**