



Starrett KCT06021RS Tungsten Carbide Tipped Holesaw Kit

(298-3222)



Features

- 8 Pc Tungsten Carbide Tipped Holesaw Kit
- Holesaw Diameters: 19mm, 25mm, 32mm, 38mm, 40mm, 51mm.
- Arbors: A1 (14-30mm), A10 (32mm-210mm)
- A cost effective solution for cutting nail embedded wood, any wood and metal combination, reinforced concrete and fibreglass.
- Leaves high quality surface finish on entry and exit and provides a smooth cut.
- Tungsten carbide tipped teeth for outstanding cutting performance and product durability.
- Suitable for use in electric and battery operated tools.
- Hole saw depth of 41mm (1-5/8").

Description

CT Hole Saws offer a cost effective solution for cutting nail embedded wood, or virtually any wood and metal combination, reinforced concrete and fibreglass. This saw is particularly suitable where there is a requirement for a high quality surface finish on the entry and exit hole and it also provides a smooth cut when cutting traditional lathe and plaster.