



H K Wentworth Group
Distributed and Supported in
the UK



hakko.com - hakko.co.uk

FM2032-52

Packing List



FM2032 Micro-Soldering Iron Handpiece (FM2032-51)
Tip **NOT** included



FH200-81 Soldering Iron Stand (Includes Cleaning
Sponge A1519)



Heat Proof Pad (B2300)



Connecting Cable (B3253)



Specifications:

FM2032 Soldering Iron

Power consumption	48W (24V)
Temperature range	200 to 450°C
Tip to ground resistance	<2Ω
Tip to ground potential	<2mV
Heating element	Composite heater
Cord length	1.3m
Total length	170mm (with 1D tip)
Weight	14g (with 1D tip)

* Total length and weight (w/o cord)

Compatibility:

Hakko FX-951	Soldering Station
Hakko FM-203	Soldering and Rework Station
Hakko FM206	Soldering and Rework Station




Is Compatible with N² Systems with the addition of a nozzle assembly purchased separately. Note: Nozzles are specific to tip shape, please see tips section.

Tips:


The FM2032 requires the T30 Series Tips which are available in a variety of shapes and sizes. Note: a Tip is NOT included with this soldering iron. Tips may be purchased separately.

Shape D




T30-D06 Shape-0.6D
N² Nozzle assembly A
(C5038)*

Shape I




T30-D1 Shape-1D
N² Nozzle assembly A
(C5038)*

Shape J




T30-J Shape-J
N² Nozzle assembly C
(C5040)*

Shape K



T30-KN Shape-KN
N² Nozzle assembly B
(C5039)*



T30-KU Shape-KU
N² Nozzle assembly A
(C5038)*

N² Nozzle assembly D (C5041) is compatible with all tip shapes and has better visibility, however it is shorter and does not supply the N² as close to the board.*

*Nozzles are only required if using Nitrogen and are not required for standard soldering applications.

Recommended Extras:



599B
Tip Cleaner



B2756
Tip Holder



Solder Wire Holder
611-1 (Single)
611-2 (Double)



FG100B
Tip Thermometer



FA-400 Desk Top
Fume Extractor



FT-710 Solder Tip
Polisher



H K Wentworth Group
Distributed and Supported in
the UK