

# Datasheet

## ECP-25 UK series

25W plug-in power supply



### Features

- No load power consumption
- Protections: short circuit//overload voltage//overload current
- UK and European versions available
- Compact and light-weight
- Withstands operating environment of 0-40°C
- Efficiencies up to 86%
- 3 year warranty
- External switch mode plug-top power supplies
- Efficiency level V, Conforms to Energy-related Product Directive 2009/125/EC
- Energy saving power supply
- Class II double insulated
- 1.2 metre (approx.) output lead with 2.1x5.5x9.5mm centre positive output connector
- Regulated output
- EMC compliance to EN 55022 Class B

Part number	Voltage	Rated current	Voltage range	Rated power	MTBF
72628I GAA	5VAA	5A	4.7 ~ 5.3V	25W	100,000hrs min. MIL-HDBK – 217F (25°C)
72628I IAA	7.5V A	3.33A	7.1 ~ 7.9V		
7262I JI	9VAA	2.78A	8.5 ~ 9.5V		
7262I JIA	12VAA	2.08A	11.4 ~ 12.6V		
7262I JGA	15VAA	1.67A	14.25 ~ 15.75V		
7262J EGA	18VAA	1.39A	17.1 ~ 18.9V		
7262J EIA	24VAA	1.04A	22.8 ~ 25.2V		

### Mechanical specification

