



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:48 (UTC)

MOTION & CONTROL
NSK



23226CKE4

Spherical Roller Bearings

Parts Number

23226CKE4C3

Boundary Dimensions


d	130	mm	Bore diameter
D	230	mm	Outside diameter
B	80	mm	Width
r (min.)	3	mm	Chamfer dimension

Basic Load Ratings

Cr	875000	N	Basic dynamic load rating
C0r	1080000	N	Basic static load rating


Speeds

Thermal Speed Rating (Oil-bath)	2000	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	2800	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	1200	min-1	Grease lubrication
Oil (Oil-bath)	1600	min-1	Oil-bath lubrication



Abutment and Fillet Dimensions

da (min.)	144	mm	Diameter of shaft abutment
da (max.)	150	mm	Diameter of shaft abutment
Da (min.)	196	mm	Diameter of housing abutment
Da (max.)	216	mm	Diameter of housing abutment
ra (max.)	2.5	mm	Radius of shaft or housing fillet



Calculation factors

e	0.34	Constant
Y2	2.9	Axial load Factors
Y3	2	Axial load Factors
Y0	1.9	Axial load Factors

Mass

Mass approx.	14.3	kg	Mass approx.
--------------	------	----	--------------

Associated products

Adapter	H2326	Adapter
Withdrawal sleeve	AHX3226	Withdrawal sleeve