


PRODUCT SHEET

195-...A

Mat chrome-plated straight nose outer circlips pliers

Right nose.

CLASSIC



reference	nozzle diameter mm	mini. Capacity mm	max. capacity mm	L mm	L"	Weight g
195-10A		8	13	139	5	97
195-13A		12	25	140	5	100
195-17A		19	60	180	7	177
195-21A		40	100	225	9	245
195-28A		85	140	310		445