

General Information

Extended Product Type:	BJM10
Product ID:	1SNA173615R2500
EAN:	3472591736151
Catalog Description:	BJM 10 10 POLES Jumper Bars
Long Description:	BJM10 - Jumper Bars - 10 poles - - 10mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

EAN:	3472591736151
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	0.027 kg
----------------------------	----------

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	155 mm
Package Level 1 Height:	5 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0,27 kg
Package Level 1 EAN:	3472591736151

Additional Information

Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Product Main Type:	BJM
Product Name:	Jumper Bar
Rated Current (I_n):	Main Circuit 57 A
Sub-Function:	Assembled jumper bar
Sub-Function 2:	Screw

Certificates and Declarations (Document Number)

GOST Certificate:	1SND161005A1103
RoHS Information:	1SND230492F0201

Classifications

E-nummer:	2925706
ETIM 4.0:	EC000489 - Cross-connector for terminal block
ETIM 5.0:	EC000489 - Cross-connector for terminal block
Object Classification Code:	X

