

Product data sheet

Specifications



SFX 304L stainless suitable enclosure, H1800xW800xD400mm, Scotch Brite® finish.

NSYSFX18840

Main

Range	Spacial
Product name	Spacial SFX
Enclosure type	Multi-purpose
Category	Suitable enclosure
Nominal height	1800 mm
Nominal width	800 mm
Nominal depth	400 mm
Product installation	Floor-standing
Device composition	1 structure 1 locking system with handle: door 4 mounting plate bracket 1 cable gland plate 1 door with reinforcement frame

Complementary

Body type	Single piece structure folded and welded Rear panel integrated
Door type	Plain
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	3 points lock, handle with 5 mm double-bar insert
Mounting plate description	Without mounting plate
Type of gland plate	Plain
Accessibility for operation	Front Side
Removable parts	Door by hinges Mounting plate bracket by screws Cable gland plate by clips
Material	Structure and door: stainless steel 304L Handle: zamak Hinge: stainless steel
Surface finish	Enclosure: Scotch-Brite® brushed Handle: painted
Net weight	90 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 62208 NEMA 4X
Product certifications	UL
IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Corrosive Specific hygiene

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	90.0 kg
Package 1 Height	50.0 cm
Package 1 width	85.0 cm
Package 1 Length	192.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------