



PW3 HI-VIS WINTER JACKET

DESCRIPTION

The stylish and functional PW3 Hi-Vis Winter Jacket will ensure you stand out from the crowd. Made from our renowned 300D Oxford PU coated durable stain resistant fabric, this jacket includes many outstanding features including the new Insulatex heat reflective lining panel, which reflects heat back into the body ensuring maximum warmth and comfort, multiple zipped pockets for secure storage, Contemporary design and modern fit.

COMPOSITION

300D Industry: 100% Polyester, 300D Oxford, Stain Resistant Finish, Double PU Coated, 190g

100% Polyester, 6060g

100% Polyester, 170g

Yellow/Grey S-3XL

FEATURES

- Waterproof with taped seams preventing water penetration
- Extremely water resistant PFAS free Texpel™ Splash Eco fabric finish, water beads away from fabric surface
- Insulatex heat reflective lining reflects heat back into the body ensuring maximum warmth and comfort
- EN342 Protection against cold certified up to -40°C
- Twin-stitched seams for extra durability
- Easy grip pullers attached to all zips
- Drawcord adjustable hem
- Curved back hem for added protection
- Quick dry knitted cuff for a snug and comfortable fit
- Hook and loop cuffs for a secure fit
- Zipped chest pocket
- 2 side zipper pockets for secure storage

STANDARDS

- EN ISO 20471 Class 2 Size XS
- EN ISO 20471 Class 3 Size S upwards
- RIS 3279 TOM Issue 2 (Orange Only)
- EN 343 Class 3:1 X WP 15,000mm
- EN 342 0.323 (M².K/W), 2, X
- ANSI/ISEA 107 Type R Class 3
- ANSI/ISEA 107 TYPE P Class 3

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
T400YGY	YELLOW/GREY	S-3XL

FEATURES



RADIO LOOPS

This symbol indicates that the garments have a radio loop for easy attachment of a radio.



PRINT ACCESS

This symbol indicates that garments have print/embroidery access.



HEAT APPLIED SEGMENTED REFLECTIVE TAPE

This symbol indicates that the garment has heat applied reflective tape



STANDARDS



EN ISO 20471
High Visibility Clothing - Test Methods
And Requirements




PERFORMANCE WORKWEAR

PW3™ contemporary workwear blends sports and lifestyle trends with function, a modern fit and improved comfort.

**GET THE
COLLECTION**



TECHINCAL INFORMATION



- Wash with similar colours
- Wash garment inside out and fully fastened

SATRA Technology Europe Ltd
(Notified Body Number.: NB: 2777)
Bracetown Business Park Clonee Dublin
15 D15 YN2P, Ireland Cert No:
2777/10990-07/E00-00

SATRA Technology Centre Ltd
(Notified Body Number.: AB: 0321) SATRA
Technology Park Wyndham Way Telford
Way Kettering Northamptonshire NN16
8SD, United Kingdom Cert No:
AB0321/17284-01/E00-00

OEKO-TEX certification
21.HMM.48610

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m ³)	EAN13	GTIN/DUN14
T400YGYS	Yellow/Grey	65	40	46	1.112	9966.666	5036108345748	15036108834294
T400GYGM	Yellow/Grey	65	40	46	1.220	9966.666	5036108345731	15036108834287
T400GYL	Yellow/Grey	65	40	46	1.270	9966.666	5036108345724	15036108834270
T400GYXL	Yellow/Grey	65	40	46	1.300	9966.666	5036108345755	15036108834300
T400GYXXL	Yellow/Grey	65	40	46	1.310	9966.666	5036108345762	15036108834317
T400GYXXXL	Yellow/Grey	65	40	46	1.420	9966.666	5036108345779	15036108834324