

RSLV216



Products Low Voltage Products and Systems Industrial Plugs and Sockets Special Plugs & Sockets
Plugs & Sockets for Extra Low Voltage

General Information

Extended Product Type:	RSLV216
Product ID:	2CMA100985R1000
EAN:	7392696009850
Catalog Description:	Industrial Socket Outlets for Surface Mounting, 2P, 16 A, 20 ... 25 AC V
Long Description:	Socket Outlet Extra low voltage for surface mounting, rated current 16A, IP44 splashproof, 2-poles, frequency 50-60 Hz, color code Purple

Additional Information

Additional Information:	2P
Color:	Purple
Connection Type:	Screw clamp
Country of Origin:	Austria (AT)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700010L0201
Declaration:	2CMC700005D0002
Declaration of Conformity - CE:	2CMC700005D0002
Degree of Protection:	IP44
E-nummer:	2417755
EAN:	7392696009850
ETIM 5:	EC001321 - CEE socket outlet
ETIM 6:	EC001321 - CEE socket outlet
Environmental Information:	2CMC700001D0002
Gross Weight:	0.198 kg
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P_#RSLV216
Minimum Order Quantity:	10 piece
Number of Poles:	2
Package Level 1 EAN:	7392696010092
Package Level 1 Gross Weight:	1.98 kg
Package Level 1 Units:	10 piece
Product Main Type:	RSLV
Product Net Depth:	119 mm
Product Net Height:	85 mm
Product Net Length:	119 mm
Product Net Weight:	0.198 kg
Product Net Width:	71 mm
Protection Type:	Splashproof
Rated Current (I_n):	16 A
Rated Voltage (U_r):	20 ... 25 AC V
Selling Unit of Measure:	piece
Short Description:	Industrial Socket Outlets for Surface Mounting, 2P, 16 A, 20 ... 25 AC V
Size:	119X85X71
Standards:	IEC 60309-1 IEC 60309-2
UNSPSC:	39120000
RAL Number:	RAL 7001 - Silver Grey

