

## FEATURES

- Portable fan heater
- Dimensions of 225 mm (H) x 165 mm (W) x 130 mm (D)
- Operating frequency of 50 Hz
- Maximum output power of 2 kW
- Air flow of 100 m<sup>3</sup>/h
- Type-C European plug
- Noise level of 45 dB(A)
- Three power settings
- On / Off switch
- Thermostatic controls

## 2kW Fan Heater, Portable, Type C - European Plug

RS Stock No.: 839-5274



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Part of the RS PRO range, this 2 kW portable fan heater features low noise operation and three heating settings. It's fitted with integrated thermostat controls for consistent warmth. It weighs only 1.54 kg, making it easy to move around and perfect for use within an office space. The fan heater has safety features including overheating protection and a thermally protected fan motor. It's also fitted with Positive Temperature Coefficient ceramic heating elements, which warm the air quickly and efficiently. The PTC increases the heater's electrical resistance when the temperature is raised, protecting it from an excessive electrical current. It's space-saving and quiet with a noise level of only 45dB – quieter than a normal conversation.

## General Specifications

<b>Heat Type</b>	Fan
<b>Air Flow</b>	100m <sup>3</sup> /h
<b>Control Type</b>	Thermostat, On/Off Switch
<b>Power Settings</b>	3
<b>Applications</b>	Automobile workshop, Construction area, Assembly operation, Food and beverage, Storeroom and workshop, Greenhouse

## Electrical Specifications

<b>Maximum Output Power</b>	2kW
<b>Voltage Rating</b>	230Vac
<b>Nominal Current</b>	8.69A
<b>Frequency</b>	50Hz
<b>Plug Type</b>	Type C - European Plug
<b>Noise Level</b>	45dB(A)

## Mechanical Specifications

<b>Mounting</b>	Portable
<b>Dimensions</b>	225mm x 165mm x 130mm
<b>Height</b>	225mm
<b>Width</b>	165mm
<b>Depth</b>	130mm
<b>Weight</b>	1.54kg

## Approvals

<b>Compliance/Certifications</b>	EN61340
----------------------------------	---------



