



Datasheet

Stock No: 113-3965

Indicator, 6.5mm Panel Mount, Recessed, Red LED, Lead Pins Termination, 3.2 mm Lamp Size, 2 V



Image representative of range

Product Details

LEDs with metal support, 33 type, board hole 7.5 mm

LED indicators for panel mounting.

The support is equipped with a 3 mm miniature LED.

Supplied with nuts and washers.

Material:	nickel-plated brass body		
Cathode marking:	Long Leg		

ref.	I lum.	IF	V _F	VF	VR	angle of	λ
Boss	(mcd)	power	power	max.	max.	diffusion	(nm)
LED 33 Red	1.5	10 mA	2 V	2.8 V	5 V	60°	697
LED 33 Green	1.5	10 mA	2 V	2.8 V	5 V	60°	560
LED 33 Yellow	1.5	10 mA	2 V	2.8 V	5 V	60°	580
LED 33 Blue	4	20 mA	3 V	3.2 V	5 V	28°	470





Specifications

Voltage Rating	2 V
Light Output Colour	Red
Mounting Hole Size	6.5mm
Lamp Size	3.2 mm
Туре	Panel Mount
Lamp Type	LED
Termination Type	Lead Pins
Bezel Style	Recessed
Bezel Colour	Chrome
Intensity	1.5 mcd
Current Rating	10 mA