

# Soft Polyurethane, Metric Size - TUS

## TUS1208N-20

### Datasheet

#### General series information

- Applicable tubing O.D.: Ø 4 to Ø 12 mm
- Operating temperature: -20 to 60 °C for air
- 8 colour variations.

#### Standard specifications

|                                        |                           |
|----------------------------------------|---------------------------|
| Size                                   | 1208 (O.D. Ø12, I.D. Ø8)  |
| Color                                  | N (Opaque)                |
| Roll Length                            | 20 m Roll                 |
| Pressure medium                        | Air                       |
| Maximum temperature of pressure medium | 20 °C                     |
| Maximum operating pressure             | 0.6 MPa                   |
| Maximum ambient temperature            | 60 °C                     |
| Minimum ambient temperature            | -20 °C (with no freezing) |
| Usable tubing material                 | Polyurethane              |
| Weight                                 | 1.400 Kg                  |

## Additional information

Catalogue

[T\\_EU.pdf](#)