

ABG 06MTL

- Part number : ABG 06MTL
- Color code : Yellow
- Body : Composite
- Nozzle : Metal
- Triger : Progressive
- Connection : ARO 210 6 mm
- Maxi temperature : +70°C
- Mini temperature : -15°C
- Impossible dust intrusion
- Concentrated blowing
- Non scratch body
- Crush resistant
- Flow @ 6 b : 20 m³/h - 11.76 cfm
- Sound level : 89 db
- Blowing force : 88 g
- Dynamic pressure : 2.2 b
- Weight : 88 g
- Advised coupling ASI 06

