



## FLAMESTAT STRETCH JACKET 4180 FSS

ART. NO: 300487

Softshell stretch material / Windproof and water repellent / Front placket opening with zip to top of collar and concealed snap fastening / Chest pocket with concealed vertical zip / 2 front pockets with concealed zip / Concealed ventilation openings at upper back / Elastic ribbon at sleeve end / Adjustable bottom with concealed snap fastening / Extended back / PFAS free / Metal free / Approved according to EN 61482-1-2 APC 2, EN 61482-1-1 ELIM: 23 cal/cm<sup>2</sup> EBT: 28 cal/cm<sup>2</sup>, EN ISO 11612 A1 A2 B1 C2 F1, EN ISO 11611 A1 A2 class 2, EN 1149-5, EN 13034 Type PB [6] and EN 13758-2 UPF 40+ UV protection. Material approved UPF 500+ UV protection / Leasing-laundry tested according to ISO 15797 / OEKO-TEX® certified.

**Material:** Stretch 47% modacrylic, 37% cotton, 12% polyurethane, 2% polyamide, 1% anti-static fibre, 1% elastane. Inherent flame protection. PFAS free.

**Weight:** 365 g/m<sup>2</sup>.

**Color:** F557 Dark navy/Neon Yellow

**Size:** S-4XL



EN 11612



EN 11611



EN 1149-5



IEC 61482-2



EN 13034



**FRISTADS®**

SIZES MAY VARY BETWEEN COLORS  
Print date: 2025-09-04