

30882

# Utility Brush, 260 mm, Medium, Green



This ergonomic, lightweight Utility brush is designed to raise the user's hand from the cleaning surface, reducing the risk of injury. Ideal for cleaning small surface areas, such as tables, pans and cutting boards.

# Technical Data

Item Number	30882
Visible bristle length	22 mm
Material	Polyester Polypropylene Stainless Steel (AISI 304)
Complies with (EC) 1935/2004 on food contact materials <sup>1</sup>	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	20 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	2080 Pcs.
Quantity Per Layer (Pallet)	160 Pcs.
Box Length	385 mm
Box Width	295 mm
Box Height	140 mm
Length/Depth	260 mm
Width	40 mm
Height	70 mm
Gross Weight	0,1 kg
Net Weight	0,09 kg
Cubik metre	0,0007 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature <sup>3</sup>	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Recycling Symbol "7", Miscellaneous Plastics	No
GTIN-13 Number	5705022000759
GTIN-14 Number (Box quantity)	15705028000767
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.