



ENGLISH

Datasheet

## RS Pro Straight Cable Mount SMC Connector, Plug, Clamp Termination, RG174 A/U

RS Stock No: 546-3428



### Product Details

RS Pro cable mount SMC connector plug includes soldered centre contact. This straight connector plug comes with a solder-cable clamp termination. It is compatible with RG174 A/U cable type.

### Features and Benefits

- Gold-plated
- Suitable for use with RG174 cable
- Centre contact is soldered

**Specifications:**

Body Orientation	Straight
Body Plating	Gold
Cable Type	RG174 A/U
Contact Material	Beryllium Copper
Contact Plating	Gold
Gender	Male
Impedance	50 $\Omega$
Mounting Type	Cable Mount
Operating Frequency	10 GHz
Size	Subminiature
Termination Method	Clamp
Dimensions	13.8 x 6.35 mm
Operating Temperature Range	-65 to +165°C