


Technical data sheet

Article number:
156-03064

T50ROSEC5B



Product Group	2-piece fixing ties for edges
Product Family	EdgeClip-Series, 1.0 - 3.0 mm, side fixing
Material	Polyamide 6.6, UV-resistant (PA66W)
Colour	Black (BK)
Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
Bundle Ø max.	45.0 mm
Bundle Ø min.	4.0 mm
Fixation Method	EdgeClip, sideways, assembled, 2 piece
Flammability	UL 94 V2
Height (H)	1.3 mm
Length (L)	200 mm
Length (L2)	14.0 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +85 °C, (+105 °C, 500 h)
Package Content packed in	bag
Pack Cont.	100 pcs.
Panel Thickness	3.0 mm
Panel Thickness min. (metric)	1.0 mm
ROHS compliant	Yes
Thickness (T)	1.3 mm
Variant	Outside Serrated
Width (W)	4.6 mm

