



Datasheet

Stock No: 123-5028

ENGLISH

# RS PRO Stainless Steel Roller Ball Cable Tie, 840 mm x 12 mm



## Description:

These stainless steel cable ties are an ideal alternative where nylon cable ties are not suitable. 316 Stainless steel has excellent resistance to abrasion, corrosion, radiation, weathering and extremes of temperature. They have a greater load carrying capacity and may be used for general strapping applications.

## Specifications:

Bundle Diameter: Min 25mm Max 250mm

Loop Tensile Strength: 1117 N (251lbf)

Operating Temperature: Min -40°C , Max 300°C

Resistant to UV Light

Plenum Rating: AH-1

Max Bundle Dia.: 250 mm