

A52.100/1, 0...200°C, 200x8mm

Bimetallic thermometer, for industrial applications A52L

Item number: 3907120

Quantity: 1 pcs.

Order code: A52.100-1-C1L-BS-C200GZZ-Z-ZZZ TD FZZVC-AZ1ZZZZZZZZZZ

Overview: A52.100/1, 0...200°C, 200x8mm
Process connection: plain, with neck to fit thermowell (thermowell necessary for mounting)
flat instrument glass
WIKA

Details: Bimetallic thermometer, for industrial applications A52L
Specifications according to data sheet: TM 52.01
Accuracy class: class 1 per EN 13190
Case: stainless steel
Stem material: stainless steel
Model: A52.100, nominal size 100, location of stem centre back
Connection design: 1, plain stem
Scale range: 0 °C ... 200 °C
Process connection: plain, with neck to fit thermowell (thermowell necessary for mounting)
Stem diameter: 8 mm
Insertion length L1: 200 mm
Window: flat instrument glass
Case: Stainless steel
Ingress protection: IP 43
Manufacturer logo: *WIKA*
Stem material: stainless steel