

## Main

Range	Odace
Product or component type	Central plate
Device presentation	Cover plate with fixing frame
Type of packing	Paint cover
Quantity per set	Set of 5





## Complementary

Wiring device mounting	Flush
Connector type	RJ45
Fixing mode	By claw kit By screws
Colour tint	White (RAL 9003)
Surface finish	Glossy
Product compatibility	Actassi s-one Infraplus
Socket number	2
Shape of screw head	Pozidriv No 1
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame
Height	71 mm
Width	71 mm
Depth	34.2 mm
Embedding depth	18.2 mm
Net weight	0.027 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

## Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
IK degree of protection	IK04

Offer Sustainability

REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#"> Yes</a>
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>