



Part Number : [1300980227](#)
Product Description : MAX-LOC Strain Relief Cord-
Sealing Grip, 3/4" NPT, Straight Male with O-Ring,
Cable Diameter 9.53-11.10mm (.375-.437")
Series Number : 130098
Status : Active
Product Category : Cable Grips
Engineering Number : 5624W



Documents & Resources

Drawings
[1300980227 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male with O-Ring, Cable Diameter 9.53-11.10mm (.375-.437")
NEMA Rating	NEMA 6P
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678856242

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	9.53-11.10mm (.375-.437")
Color - Grommet	Green
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	74.138/kg
Number of Holes	1

O-Ring	Yes
Thread Size	3/4" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/4" NPT	<u>1300990144</u>