

MLFB-Ordering data

6SE6400-3TC00-4AD2



Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Rated current	4.00 A	<b>Power connection Power Module</b>	
Power loss	0.005 kW	Version	Pigtail
Mechanical data		Length	0.35 m
Width	75.5 mm (2.97 in)	<b>Power connection motor</b>	
Height	200.0 mm (7.87 in)	Version	screw terminals
Depth	110.0 mm (4.33 in)	Conductor cross-section	2.50 mm <sup>2</sup>
Degree of protection	IP20 / UL open type	<b>Max. motor cable length</b>	
Net weight	1.90 kg (4.19 lb)	3 AC 380 V -10 % ... 400 V	
		Shielded	150 m
		Unshielded	225 m
		3 AC 401 V ... 480 V +10 %	
		Shielded	100 m
		Unshielded	150 m
		<b>PE connection</b>	
		Version	M5 stud