

FEATURES

- Durable and lightweight
- Corrosion resistant
- Resistant to greases and oils
- Good electrical and thermal insulating properties
- Resistant to a wide range of temperatures

RS PRO, M3 Countersunk Head, 10mm Nylon Slot Plain

RS Stock No.: 291-363



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO a high-quality machine screw with a flat countersunk head for flush fitting. The screw head is slotted for easy tightening with a flat blade screwdriver. This machine screw has a metric thread and is made from high-quality nylon making it strong, lightweight and resistant to corrosion. Nylon also has excellent electrical insulation properties making this machine screw ideal for use in electronics applications.

General Specifications

Head Shape	Countersunk
Drive Type	Slot
Applications	Washing machines, Household appliances, Handheld devices, Electronics and circuit boards, Commercial machinery, Automotive parts

Mechanical Specifications

Thread Size (Metric)	M3
Length Metric	10mm
Material	Nylon 66
Finish	Plain
Thread Pitch	0.5mm
Specification	BS 4183

