

Eaton 12TDLEJ6.3

Catalog Number: 12TDLEJ6.3

Eaton Bussmann series medium voltage DIN fuse, 6.3 A, AC 12 kV, 2", 51 x 292 mm, backup, DIN, with striker

Spécifications générales



Product Name

Eaton Bussmann series medium voltage
DIN fuse

Catalog Number

12TDLEJ6.3

EAN

5027590516471

UPC

051712186032

Product Length/Depth

292 mm

Product Height

54 mm

Product Width

51 mm

Product Weight

1568 g

Compliances

DIN 43625

VDE 0670-4

IEC 60282-1

Caractéristiques du produit

Ressources

Used with

270303 Fuse clip

A3354710 Fuse clip

Type

Fuse

Application

transformer protection

indoor or outdoor use

Amperage Rating

6.3 A

Fuse indicator

With Striker

Fuse size

51 x 292 mm

Breaking capacity

63 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

DIN

Utilization category

Other

Voltage type

AC

With striker

Yes

Class

Class back-up

Barrels

1

Construction type

Bolt-on

Pre arc (I2T)

9.8 x 10

Resistance

222 Ohms

Watt losses

10 W

Fuse diameter

51 mm

Interrupt rating

63 kAIC

Construction size

51 x 292 mm

Mounting method

Clip-in

Packaging type

Standard

Voltage rating

12 kV

Fuse type

TDLEJ

droits réservés.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)